

DATASHEET

CATEGORY: APLIWELD® Multiple mould
 NAME: **Multiple mould for cable/tape/rod ø15.9**
 REFERENCE: **MM-CT16**



PRODUCT DESCRIPTION

Case containing Multiple Mould and accessories for 40-60 weldings for cable/cable (up to 95 mm²); tape/cable (up to 95 mm²), tape/tape and those conductors to ø15.9 mm rod.



> Application



- > The multiple mould is the best solution if only a few common welding types are required, when the features of the work to be carried out cannot be predicted, when conductor sizes are variable or in case of any unexpected occurrences during installation.
- > Multiple mould is aimed for horizontal T, cross and earth rod welding. However, in some cases it can also weld straight and parallel bonds.
- > It is adapted for both electronic starter (APLIWELD-E®) and starting powder ignition types.
- > The product is supplied in a case that contains all the necessary materials to carry out the welding, except for the consumables (tablets and igniters).
- > The MM-CS cavity sealants are, along with the tablets, the consumables involved in the process. MM-CS are supplied in packets of 60 units. They form the welding cavity and are placed according to the table of connections.
- > Graphite moulds can withstand at least 80 welds.
- > Read the instructions provided with all multiple mould cases or the APLIWELD® manual.

DATASHEET

Reference	MM-CT16
Cables	up to 95 mm²
Tapes	up to 30 mm
Rod	ø15.9 mm

> References included:

MM-PT16	Lower part for ø15.9 mm earth rod
MM-053N	Multiple mould clamp
MM-T	Multiple mould crucible
MM-CS	Cavity sealers (60 units)
AT-080N	Multiple mould case
AT-060N	Spark lighter (for powder starter)
AT-061N	Conductor cleaning brush
AT-062N	Crucible and electronic starter cavity cleaning brush
AT-063N	Slag removal spade
AT-064N	Welding cavity cleaning brush
AT-065N	Sealing paste to prevent material leaking
AT-073N	Safety gloves
AT-082N	Vertical stand pliers for earth rod welding
MM-PH	Lower part for cable and tape welding

INSTRUCTIONS

> SAFETY AND MAINTENANCE

Read carefully the particular product instructions supplied in all Apliweld® products before its use.

All personnel that will carry out Apliweld exothermic welding should be duly trained in the correct usage of the product.

OTHER INFORMATION

> ACCESSORIES



MM-T
Multiple mould crucible



AT-062N
Crucib&Elec.starters cover
cleaning brush



AT-063N
Slag removal spade



AT-064N
Weld cavity cleaning
brush



MM-053N
Standard multiple clamp



MM-PT16
MM lower piece for
cable/tape/ ø16 rod



MM-PH
MM lower piece for
cable/tape

> RELATED PRODUCTS



AT-020N
Apliweld®-T: 20 welding
tablets ø43mm



AT-010N
Apliweld®-E. Electronic
starter 10 units



AT-200N
Kit Apliweld®-E v.3:
Electronic ignition kit



MM-CS
Cavity sealers (60 units)